

METHOD 5 PUMP ASSEMBLIES

Lubricated Rotary Vane Pump (0523)

The Lubricated Rotary Vane Pump includes a 5' power cord and 2 wire-reinforced, kink-free hoses with nonreversible stainless steel quick connects. The pump is mounted in our standard durable, RotoMolded Plastic Enclosure X-Case with removable covers providing easy access for service. The wick style lubricator requires less maintenance. Option "V" added for 240V.



XE-0523

Specifications

- Motor: 1/4hp, 120/240V 60/50Hz 4.6/2.3 Amp., RPM 1725/1425
- Measured Flow: 3.1 cfm@ 1 inch Hg;
1.5 cfm@ 15 inches Hg
- Maximum Vacuum: 25.5" Hg
- Weight: 35 lbs., (16kg)

XE-0523 Rotary Vane Pumps

Model	Description
XE-0523	Rotary Vane Pump in a Molded X-Case (120V/ 60 Hz)
XE-0523-V	Rotary Vane Pump in a Molded X-Case (240V/ 50Hz)



METHOD 5 PUMP ASSEMBLIES

Double Headed Diaphragm Pump (DAA)

The Double Headed Diaphragm Pump will never require any lubrication. Pump is easy to service within its frame and includes a power cord, two 5' wire-reinforced, kink-free hoses with non-reversible stainless steel quick connects (*this pump is not recommended for use in extremely cold environments*).



XE-DAA

Specifications

- Motor: 1/2hp, 120V/60Hz, 5 1/2 Amp
- Measured Flow: 2.9 cfm@ 1 inch Hg;
1.4 cfm@ 15 inches Hg
- Maximum Vacuum: 26.5" Hg
- Weight: 30 lbs., (14kg)

XE-DAA Pumps Diaphragm Pumps

Model	Pump
XE-DAA	Double Headed Diaphragm Pump in a Molded X-Case, 110V/60Hz
XE-DAA-V	Double Headed Diaphragm Pump in a Molded X-Case, 220V/50Hz



For more information, contact us :

Pacwill Environmental

905.563.9097

Toll-Free (Canada): 1-866-840-0014

sales@pacwill.ca

www.pacwill.ca

